

HUVITZ APPLANATION TONOMETER

HT-5000





HUVITZ APPLANATION TONOMETER HT-5000

- The world standard Goldmann applanation tonometer
- The digital display makes it easy to read even in a dark room.
- The wide grip comfortable knob for easier adjustment of measuring prism
- Optimized algorithm realizes the fast process of IOP calculation.
- Instantaneous wake-up time from sleep mode!
- The power supply by the most commonly used AAA batteries guarantees easy installation and maintenance.
- The slanted display matches to the angle of a user's view for more comfortable observation.

SPECIFICATIONS

Measuring force	generated by leverage weight
Installation	Mountable on peg on microscope.
Measuring range	3~75mm Hg
Measurement divergence	Of the force Impingement on the measuring prism over a measuring range from 0-58.84 mN
Standard divergence	0.49 mN $\neq$ /< 3 s $\neq$ /< 1.5 % of rated value
Reverse span	$\neq$ /< 0.49 mN
Power Consumption	DC3V
Net weight	0.50kg (without accessories, with batteries)

Designs and details can be changed without prior notice for the purposes of improvement.

Huvitz

Huvitz Building 689-3, Geumjeong-dong
Gunpo-si, Gyeonggi-do, 435-862, Korea

Tel : +82-31-442-8868

Fax : +82-31-477-8617

http : // www.huvitz.com

Distributed by